



Product designation	Protocol converter		
Product type designation	EXCCON02		
General characteristics			
Description	RS485-Ethernet Modbus protocol converter		
Functions	RS485/Ethernet		
Rated power supply voltage	9...48VDC, 24VAC		
Communications			
Type of communication port	RS485/Ethernet		
Protocols supported	Modbus, Serial device TCP server/client		
Monitoring method			
Transmission technology	Ethernet/TCP		
Device setup and supervision	Webserver		
Interface			
RS232 communication	Yes		
RS485 communication	Yes		
Ethernet communication	Yes		
Mobile communication	No		
Mechanical features			
Fixing	DIN rail or rear mounting		
Weight	g	430	
Ambient conditions			
Temperature	Operating temperature		
	min	°C	-40
	max	°C	+75
Certifications and compliance			
Certifications	IEC/EN/BS 55024		
	IEC/EN/BS 55032		
	IEC/EN/BS 55035		
Compliance	EAC		
	UCKA		
ETIM classification			
EC000066 - Power contactor, AC switching			