



**AC coil operating**

Rated AC voltage at 60Hz V 230

|                      |                              |     |     |     |
|----------------------|------------------------------|-----|-----|-----|
| AC operating voltage |                              |     |     |     |
|                      | of 60Hz coil powered at 60Hz |     |     |     |
|                      | pick-up                      | min | %Us | 80  |
|                      |                              | max | %Us | 110 |
|                      | drop-out                     | min | %Us | 20  |
|                      |                              | max | %Us | 55  |

|                                     |                              |         |    |    |
|-------------------------------------|------------------------------|---------|----|----|
| AC average coil consumption at 20°C |                              |         |    |    |
|                                     | of 60Hz coil powered at 60Hz |         |    |    |
|                                     |                              | in-rush | VA | 75 |
|                                     |                              | holding | VA | 9  |

Dissipation at holding ≤20°C 50Hz W 2.5

**Certifications and compliance**

Certificates /

**ETIM classification**

ETIM 8.0 EC002563 - Coil for low-voltage