



**AC coil operating**

Rated AC voltage at 50/60Hz, 60Hz

min	V	60
max	V	110

AC operating voltage

of 50/60Hz coil powered at 50Hz  
pick-up

min	%Us	80 Us min
max	%Us	110 Us max

drop-out

max	%Us	≤70 Us min
-----	-----	------------

of 50/60Hz coil powered at 60Hz  
pick-up

min	%Us	80 Us min
max	%Us	110 Us max

drop-out

max	%Us	≤70 Us min
-----	-----	------------

AC average coil consumption at 20°C

of 50/60Hz coil powered at 50Hz

in-rush	VA	35...120
holding	VA	1.5...3.7

of 50/60Hz coil powered at 60Hz

in-rush	VA	35...120
holding	VA	1.5...3.7

Dissipation at holding ≤20°C 50Hz

W	1...2.5
---	---------

**Certifications and compliance**

Certificates

/

**ETIM classification**

ETIM 8.0

EC002563 - Coil  
for low-voltage