DM3T0250

CURRENT TRANSFORMER, SOLID-CORE, FOR Ø30MM CABLE. FOR 40X10MM, 30X20MM, 25X25MM BUSBARS, 250A

Current inputs			
Primary current Ipn (/5)		A	250
Operational frequency			
	min	Hz	50
	max	Hz	60
Secondary output current		A	5
Overload withstand Ipn		%	120
Burden			
	cl. 1	VA	5
Insulations			
Rated insulation voltage Ui IEC/EN		V	720
IEC rated short-time thermal current Ith		Ith for s	40…60
IEC rated dynamic current Idyn		Ith for s	2.5
Insulation dry type			Class E
Mechanical features			
Terminals type			Faston
Fixing			DIN rail or by Screw
Weight		g	260
Ambient conditions			
Temperature			
Operating temperature			
	min	°C	-25
	max	°C	+50
Storage temperature			
	min	°C	-40
	max	°C	+80
Relative humidity		%	90
Protection degree			IP30
Dimensions			

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding

DM3T0250

CURRENT TRANSFORMER, SOLID-CORE, FOR Ø30MM CABLE. FOR 40X10MM, 30X20MM, 25X25MM BUSBARS, 250A



Certifications and compliance

Certifications

	IEC/EN/BS 61869-1
	IEC/EN/BS 61869-2

Compliance

	EAC

ETIM classification

EC000066 - Power contactor, AC switching

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding