



Product designation

Reversing
 contactor

Product type designation

BFA018

Contact characteristics

Operational current I_e

AC-3 (≤440V ≤55°C) A 18

Rated operational power AC-3 (T≤55°C)

230V	kW	4
400V	kW	7.5
415V	kW	9
440V	kW	9
500V	kW	10
690V	kW	10

Built-in auxiliary contacts

NO	0
NC	1

UL technical data

Maximum UL/CSA horsepower ratings single-phase

110V-120V	HP	1
220V-240V	HP	3

Maximum UL/CSA horsepower ratings three-phase, 3-pole

200V-208V	HP	5
220V-240V	HP	5
440V-480V	HP	10
550V-600V	HP	15

Mechanical features

Terminals type

Clamp screw

Weight

g 760

ETIM classification

ETIM 8.0

EC001037 -
 Motor
 starter/Motor
 starter
 combination