



Product designation Star-delta starter
Product type designation BFA018

Electrical features

Maximum operating current ($\leq 440V$) A 28

Components

Contactor standard supplied BF1810A / BF1801A / BF1210A
Thermal relay standard supplied No
Thermal relay to purchase separately RF38
Auxiliary contact standard supplied BFX1020 // BFX1011

Contact characteristics


IEC standard motor powers

230V	kW	7.5
400V	kW	15
440V	kW	11
500V	kW	11

Mechanical features



Weight g 1700

Dimensions



STARTER TYPE	A	B
BFA009 70	130.5 (5.14")	109.5 (4.31")
BFA012 70	130.5 (5.14")	109.5 (4.31")
BFA018 70	130.5 (5.14")	109.5 (4.31")
BFA025 70	130.5 (5.14")	109.5 (4.31")
BFA026 70	135 (5.14")	119 (4.68")
BFA032 70	135 (5.14")	119 (4.68")
BFA038 70	135 (5.14")	119 (4.68")
BFA050 70	173 (6.81")	142 (5.59")
BFA065 70	173 (6.81")	142 (5.59")
BFA080 70	183 (7.20")	142 (5.59")

Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-9

Certificates

/

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination