



Product designation	Direct-on-line starter		
Product type designation	M0P00910		
<b>Electrical features</b>			
Maximum operating current ( $\leq 440V$ )	A	10	
<b>Components</b>			
Starter enclosure standard supplied	M0PA		
Contactors standard supplied	BG0910A		
Thermal relay to purchase separately	RF9...		
<b>Mechanical features</b>			
Weight	g	667	
<b>Ambient conditions</b>			
Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70
<b>Resistance &amp; Protection</b>			
Frontal IP degree	IP65		
<b>ETIM classification</b>			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		