



Product designation	Direct-on-line starter		
Product type designation	M0P00910		
Electrical features			
Maximum operating current ($\leq 440V$)	A	10	
Components			
Starter enclosure standard supplied	M0PA		
Contacteur standard supplied	BG0910A		
Thermal relay to purchase separately	RF9...		
Mechanical features			
Weight	g	667	
Ambient conditions			
Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70
Resistance & Protection			
Frontal IP degree	IP65		
ETIM classification			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		