



Product designation	Direct-on-line starter		
Product type designation	M0P00912...1V5		
<b>Electrical features</b>			
Relay adj range	A	0.9-1.5	
IEC technical characteristics ( $\leq 440V$ )			
	le	A	1.5
	kW	kW	0.37
<b>Components</b>			
Starter enclosure standard supplied	M0PA		
Contactors standard supplied	BG0910A		
Thermal relay standard supplied	RF91V5		
<b>UL technical data</b>			
Maximum UL/CSA horsepower ratings three-phase, 3-pole			
	440V-480V	HP	0.75
	550V-600V	HP	0.75
<b>Mechanical features</b>			
Weight	g	760	
<b>Ambient conditions</b>			
Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70
<b>Resistance &amp; Protection</b>			
Frontal IP degree	IP65		
<b>ETIM classification</b>			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		