



Product designation	Direct-on-line starter		
Product type designation	M0R00912...5		
Electrical features			
Relay adj range	A	0,3-0,5	
IEC technical characteristics ($\leq 440V$)			
	le kW	A kW	5 1.5...2.2
Components			
Starter enclosure standard supplied	MORA		
Contactors standard supplied	BG0910A		
Thermal relay standard supplied	RF95		
Mechanical features			
Weight	g	720	
Ambient conditions			
Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70
Resistance & Protection			
Frontal IP degree	IP65		
ETIM classification			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		