



Product designation				Direct-on-line starter
Product type designation				M1P00912...A7
Electrical features				
Relay adj range		A	2.5-4	
IEC technical characteristics ($\leq 440V$)				
	le	A	4	
	kW	kW	1.1...1.5	
Components				
Starter enclosure standard supplied				M1PA
Contactors standard supplied				BF0910A
Thermal relay standard supplied				RF380400
UL technical data				
Maximum UL/CSA horsepower ratings three-phase, 3-pole				
	200V-208V	HP	0.75	
	220V-240V	HP	0.75	
	440V-480V	HP	2	
	550V-600V	HP	3	
Mechanical features				
Weight				g 1040
Ambient conditions				
Operating temperature				
	min	°C	-25	
	max	°C	+60	
Storage temperature				
	min	°C	-40	
	max	°C	+70	
Resistance & Protection				
Frontal IP degree				IP65
ETIM classification				
ETIM 8.0				EC001037 - Motor starter/Motor starter combination