



Product designation	Direct-on-line starter		
Product type designation	M25P03812...B5		
Electrical features			
Relay adj range	A	32-38	
IEC technical characteristics ($\leq 440V$)			
	le	A	38
	kW	kW	18.5
Components			
Starter enclosure standard supplied	M25PA		
Contactors standard supplied	BF3800A		
Thermal relay standard supplied	RF383800		
UL technical data			
Maximum UL/CSA horsepower ratings single-phase			
	110V-120V	HP	3
	220V-240V	HP	7.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole			
	200V-208V	HP	10
	220V-240V	HP	15
	440V-480V	HP	30
	550V-600V	HP	30
Mechanical features			
Weight	g	2880	
Ambient conditions			
Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70
Resistance & Protection			
Frontal IP degree	IP65		
ETIM classification			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		