M2P00911400B0

DIRECT-ON-LINE-STARTER, ENCLOSED WITH MOTOR PROTECTION CIRCUIT BREAKER, 13A (≤440V), IP65. CONTACTOR COIL VOLTAGE 400VAC 50/60HZ

Electrical features			
Relay adj range		A	9-14
IEC technical characteristics (≤440V)			
	Ie	A	13
	kW	kW	5.5
UL technical data			
UL degree of protection			Type 1, 12K, 4, 4X
Mechanical features			
Weight		g	1515
Ambient conditions			
Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70
Resistance & Protection			
IEC degree of protection			IP65
Dimensions			

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding



Wiring diagrams

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding

Incorporated button control and rotary actuator for 3-phase motors



I = Start; O = Stop; E = Emergency Stop

Power connection for 1-phase motors



Certifications and compliance

Compliance

	IEC/EN 60947-1
	IEC/EN 60947-4-1

Certificates

	EAC

ETIM classification

ETIM 8.0	EC001037 - Motor starter/Motor starter combination

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding