



Product designation	Direct-on-line starter		
Product type designation	M2P02512...B2		
<b>Electrical features</b>			
Relay adj range	A	17-23	
IEC technical characteristics ( $\leq 440V$ )			
	le	A	23
	kW	kW	11
<b>Components</b>			
Starter enclosure standard supplied	M2PA		
Contactors standard supplied	BF2510A		
Thermal relay standard supplied	RF382300		
<b>UL technical data</b>			
Maximum UL/CSA horsepower ratings single-phase			
	110V-120V	HP	1.5
	220V-240V	HP	3
Maximum UL/CSA horsepower ratings three-phase, 3-pole			
	200V-208V	HP	5
	220V-240V	HP	7.5
	440V-480V	HP	15
	550V-600V	HP	15
<b>Mechanical features</b>			
Weight	g	1220	
<b>Ambient conditions</b>			
Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70
<b>Resistance &amp; Protection</b>			
Frontal IP degree	IP65		
<b>ETIM classification</b>			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		