





Product designation	Direct-on-line starter		
Product type designation	M2R02512...B2		
<b>Electrical features</b>			
Relay adj range	A	17-23	
IEC technical characteristics ( $\leq 440V$ )			
	le	A	23
	kW	kW	11
<b>Components</b>			
Starter enclosure standard supplied	M2RA		
Contactor standard supplied	BF2510A		
Thermal relay standard supplied	RF382300		
<b>Mechanical features</b>			
Weight	g	1165	
<b>Ambient conditions</b>			
Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70
<b>Resistance &amp; Protection</b>			
Frontal IP degree	IP65		
<b>Dimensions</b>			



Wiring diagrams



R = Reset; I = Start; O = Stop

### Certifications and compliance

#### Compliance

IEC/EN 60947-1  
IEC/EN 60947-4-1  
UL508 CSA C22.2 n° 14

#### Certificates

CSAus  
cULus  
EAC

### ETIM classification

ETIM 8.0

EC001037 -  
Motor  
starter/Motor  
starter  
combination