

STAR-DELTA STARTER, ENCLOSED STARTER, WITH SWITCH DISCONNECTOR, ROTARY DOOR COUPLING HANDLE GAX61 AND START AND STOP/RESET BUTTONS. STARTING TIME UP TO 12 SECONDS AND A MAXIMUM OF 30 OPERATIONS/HOUR, MAX IEC OPERATING CURRENT 22A. COIL VOLTAGE 400VAC 50/60HZ



Product designation	Enclosed star-delta starters		
Product type designation	M3P01273		
Electrical features			
Maximum operating current ($\leq 440V$)	A	22	
Components			
Starter enclosure standard supplied	M3PA70		
Contactor standard supplied	BF1210A, BF1201A, BF0910A		
Thermal relay to purchase separately	RF38...		
Auxiliary contact standard supplied	BFX1020, ..., BFX1011		
Mechanical features			
Weight	g	3700	
Ambient conditions			
Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70
Resistance & Protection			
Frontal IP degree	IP65		
ETIM classification			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		