

STAR-DELTA STARTER, ENCLOSED STARTER, WITH SWITCH DISCONNECTOR, ROTARY DOOR COUPLING HANDLE GAX61 AND START AND STOP/RESET BUTTONS. STARTING TIME UP TO 12 SECONDS AND A MAXIMUM OF 30 OPERATIONS/HOUR, MAX IEC OPERATING CURRENT 35A. COIL VOLTAGE 400VAC 50/60HZ



Product designation				Enclosed star-delta starters
Product type designation				M3P02573
Electrical features				
Maximum operating current ($\leq 440V$)	A			35
Components				
Starter enclosure standard supplied				M3PA70
Contactor standard supplied				BF2510A, BF2501A, BF1810A
Thermal relay to purchase separately				RF38...
Auxiliary contact standard supplied				BFX1020, ..., BFX1011
Mechanical features				
Weight	g			3800
Ambient conditions				
Operating temperature	min	°C	-25	
	max	°C	+60	
Storage temperature	min	°C	-40	
	max	°C	+70	
Resistance & Protection				
Frontal IP degree				IP65
ETIM classification				
ETIM 8.0				EC001037 - Motor starter/Motor starter combination