

STAR-DELTA STARTER, ENCLOSED STARTER, WITH SWITCH DISCONNECTOR, ROTARY DOOR COUPLING HANDLE GAX61 AND START AND STOP/RESET BUTTONS. STARTING TIME UP TO 12 SECONDS AND A MAXIMUM OF 30 OPERATIONS/HOUR, MAX IEC OPERATING CURRENT 50A. COIL VOLTAGE 230VAC 50/60HZ



Product designation				Enclosed star-delta starters
Product type designation				M3P03273
<b>Electrical features</b>				
Maximum operating current ( $\leq 440V$ )	A			50
<b>Components</b>				
Starter enclosure standard supplied				M3PA70
Contactor standard supplied				BF3200A, BF3200A, BF2510A
Thermal relay to purchase separately				RF38...
Auxiliary contact standard supplied				BFX1020, BFX1011, BFX1011
<b>Mechanical features</b>				
Weight	g			4300
<b>Ambient conditions</b>				
Operating temperature	min	°C	-25	
	max	°C	+60	
Storage temperature	min	°C	-40	
	max	°C	+70	
<b>Resistance &amp; Protection</b>				
Frontal IP degree				IP65
<b>ETIM classification</b>				
ETIM 8.0				EC001037 - Motor starter/Motor starter combination