

STAR-DELTA STARTER, ENCLOSED STARTER, WITH SWITCH DISCONNECTOR, ROTARY DOOR COUPLING HANDLE GAX61 AND START AND STOP/RESET BUTTONS. STARTING TIME UP TO 12 SECONDS AND A MAXIMUM OF 30 OPERATIONS/HOUR, MAX IEC OPERATING CURRENT 60A. COIL VOLTAGE 400VAC 50/60HZ



Product designation	Enclosed star-delta starters		
Product type designation	M3P03273		
<b>Electrical features</b>			
Maximum operating current ( $\leq 440V$ )	A	60	
<b>Components</b>			
Starter enclosure standard supplied	M3PA70		
Contactor standard supplied	BF3800A, BF3800A, BF2510A		
Thermal relay to purchase separately	RF38...		
Auxiliary contact standard supplied	BFX1020, BFX1011, BFX1011		
<b>Mechanical features</b>			
Weight	g	4300	
<b>Ambient conditions</b>			
Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70
<b>Resistance &amp; Protection</b>			
Frontal IP degree	IP20		
<b>ETIM classification</b>			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		