

Product designation	Direct-on-line starter		
Product type designation	M3P06512...B7		
Electrical features			
Relay adj range	A	45-65	
IEC technical characteristics ($\leq 440V$)			
	le	A	65
	kW	kW	30
Components			
Starter enclosure standard supplied	M3PA		
Contactors standard supplied	BF6500A		
Thermal relay standard supplied	RF826500		
UL technical data			
Maximum UL/CSA horsepower ratings three-phase, 3-pole			
	200V-208V	HP	20
	220V-240V	HP	25
	440V-480V	HP	50
	550V-600V	HP	60
Mechanical features			
Weight	g	3760	
Ambient conditions			
Operating temperature			
	min	°C	-25
	max	°C	+60
Storage temperature			
	min	°C	-40
	max	°C	+70
Resistance & Protection			
Frontal IP degree	IP65		
ETIM classification			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		