



Product designation				Metal mounting plate for M3N
Product type designation				MX30
Mechanical features				
Weight		g	500	
Ambient conditions				
Operating temperature	min	°C	-25	
	max	°C	+60	
Storage temperature	min	°C	-40	
	max	°C	+70	
Resistance & Protection				
Frontal IP degree				IP65
Certifications and compliance				
Compliance	CSA C22.2 n° 14			
	IEC/EN 60947-1			
	IEC/EN 60947-4-1			
	UL508			
Certificates	cULus			
	ETIM classification			
ETIM 8.0				EC002498 - Accessories/spare parts for low-voltage switch technology