



Metal mounting plate for M24N and M25 enclosures MX31

Product designation

Product type designation

Mechanical features

Weight g 400

Ambient conditions

Operating temperature

min °C -25
max °C +60

Storage temperature

min °C -40
max °C +70

Resistance & Protection

Frontal IP degree IP65

Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN 60947-1
IEC/EN 60947-4-1
UL508

Certificates

cULus

ETIM classification

ETIM 8.0

EC002498 -
Accessories/spare parts for low-voltage switch technology