

STAR-DELTA STARTER, ENCLOSED STARTER, WITH SWITCH DISCONNECTOR, ROTARY DOOR COUPLING HANDLE GAX61 AND START AND STOP/RESET BUTTONS. STARTING TIME UP TO 12 SECONDS AND A MAXIMUM OF 30 OPERATIONS/HOUR, MAX IEC OPERATING CURRENT 16A. COIL VOLTAGE 230VAC 50/60HZ



Denumirea produsului	Starter stea-triunghi		
Denumirea tipului de produs	M3P00973		
Caracteristici electrice			
Curent maxim de funcționare ($\leq 440V$)	A	16	
Componente			
Carcasa de pornire standard furnizată	M3PA70		
Contactora standard furnizat	BF0910A, BF0901A, BF0910A		
Releul termic se achiziționează separat	RF38...		
Standard de contact auxiliar furnizat	BFX1020, ..., BFX1011		
Caracteristici mecanice			
Greutate	g	3700	
Condiții ambientale			
Temperatura de Operare	Temperatura min	°C	-25
	Temperatura max	°C	+60
Temperatura de depozitare	Temperatura min	°C	-40
	Temperatura max	°C	+70
Rezistență și protecție			
Grad IP frontal	IP65		
Clasificare ETIM			
ETIM 8.0	EC001037 - Combinatie starter motor/starter motor		