

STAR-DELTA STARTER, ENCLOSED STARTER, WITH SWITCH DISCONNECTOR, ROTARY DOOR COUPLING HANDLE GAX61 AND START AND STOP/RESET BUTTONS. STARTING TIME UP TO 12 SECONDS AND A MAXIMUM OF 30 OPERATIONS/HOUR, MAX IEC OPERATING CURRENT 43A. COIL VOLTAGE 24VAC 50/60HZ



| | | | |
|---|---|------|-----|
| Denumirea produsului | Starter stea-triunghi | | |
| Denumirea tipului de produs | M3P02673 | | |
| Caracteristici electrice | | | |
| Curent maxim de funcționare ($\leq 440V$) | A | 43 | |
| Componente | | | |
| Carcasa de pornire standard furnizată | M3PA70 | | |
| Contactator standard furnizat | BF2600A, BF2600A, BF1810A | | |
| Releul termic se achiziționează separat | RF38... | | |
| Standard de contact auxiliar furnizat | BFX1020, BFX1011, BFX1011 | | |
| Caracteristici mecanice | | | |
| Greutate | g | 3800 | |
| Conditii ambientale | | | |
| Temperatura de Operare | Temperatura min | °C | -25 |
| | Temperatura max | °C | +60 |
| Temperatura de depozitare | Temperatura min | °C | -40 |
| | Temperatura max | °C | +70 |
| Rezistență și protecție | | | |
| Grad IP frontal | IP65 | | |
| Clasificare ETIM | | | |
| ETIM 8.0 | EC001037 - Combinăție starter motor/starter motor | | |