



Product designation	Electronic current transformers for EASY BRANCH system
Product type designation	EXS3032
Type	Three-phase

**Current inputs**

Rated current (Ie)	A	32
--------------------	---	----

**Current**

IEC maximum (Imax)	A	32
IEC rated (Iref-Ib)	A	5
IEC start (Ist)	mA	10

**Insulations**

Rated insulation voltage Ui IEC/EN	V	600
------------------------------------	---	-----

**Mechanical features**

Housing type	Polyamide
Terminals type	RJ45
Weight	g 140

**Ambient conditions**

Temperature	Operating temperature	min	°C	-30
		max	°C	+70
	Storage temperature	min	°C	-30
		max	°C	+80


Relative humidity	%	<80
-------------------	---	-----

Maximum Pollution degree	2
--------------------------	---

Overvoltage category	3
----------------------	---

Protection degree	IP20
-------------------	------

**Dimensions**



**Certifications and compliance**

Compliance	IEC/EN/BS 61000-6-2
	IEC/EN/BS 61000-6-4
	IEC/EN/BS 61010-1

**Certificates**

CE

cETLus

EAC

UKCA

ETIM classification

ETIM 8.0

EC002475 -  
Current value  
transformer