



Contact characteristics				
Rated insulation voltage Ui IEC/EN			V	250
Rated impulse withstand voltage Uimp			kV	4
Mechanical features				
Socket screw tightening tool (cross / flat blade)				Phillips 1/4.5mm
Conductor section				
AWG/Kcmil			min	20
			max	14
IEC			min	mm² 0.5
			max	mm² 2.5
Fixing				On 35mm DIN rail
Certifications and compliance				
Compliance				
IEC/EN/BS 61810-1				
Certificates				
cURus				
TUV				
ETIM classification				
ETIM 8.0				EC001456 - Relay socket