



Contact characteristics

Rated insulation voltage U_i IEC/EN	V	250
Rated impulse withstand voltage U_{imp}	kV	4

Mechanical features

Socket screw tightening tool (cross / flat blade)	Phillips 1/4.5mm
---	------------------

Conductor section				
AWG/Kcmil				
		min	20	
		max	14	
IEC				
		min	mm ²	0.5
		max	mm ²	2.5

Fixing	On 35mm DIN rail
--------	------------------

Certifications and compliance

Compliance	IEC/EN/BS 61810-1
------------	-------------------

Certificates	cURus
	TUV

ETIM classification

ETIM 8.0	EC001456 - Relay socket
----------	-------------------------