




Product designation	Float switches for grey water		
Product type designation	LVFSN1		
Function	Emptying or filling		
<b>Counterweights</b>			
Counterweight	External (provided with the float switch)		
Activation angle	45°		
<b>Relay outputs</b>			
Number of relays	Nr.	1	
Contact arrangement	1 changeover contact C/O-SPDT		
Rated operational voltage AC (IEC)	VAC	250	
Contact ratings	AC1 10A 250VAC AC15 8A 250VAC		
<b>Connections</b>			
Maximum cable length	m / ft	3	
<b>Ambient conditions</b>			
Temperature	Operating temperature		
	max	°C	+40
	Storage temperature		
	max	°C	+80
Maximum operating pressure	bar	3	
Maximum installation depth	m	30	
<b>Housing</b>			
Cable material	Neoprene H07 RN-F3X1		
Float casing material	Polypropylene		
IEC degree of protection	IP68		
Weight	g	640	
<b>Dimensions</b>			



**Certifications and compliance**

Compliance

IEC/EN 60730-1  
 IEC/EN 60730-2-15

Certificates

TÜV-SUD

**ETIM classification**

ETIM 8.0

EC001447 - (Fill)  
 level monitoring  
 relay