




Product designation	AUXILIARY CONTACTS		
Product type designation	CNB		
Number of DIN modules	0.5		
Electrical features			
IEC Conventional free air thermal current I _{th}	A	4	
Rated impulse withstand voltage U _{imp}	kV	4	
Minimum switching capacity	≥12V ≥5mA		
Control circuit			
Auxiliary contacts	NO	Nr.	1
	NC	Nr.	1
Operations			
Mechanical life		cycles	3000000
Ambient conditions			
Operating temperature	min	°C	-5
	max	°C	55
Storage temperature	min	°C	-30
	max	°C	80
Max altitude		m	2000
Mechanical features			
Tightening torque for terminals	max	Nm	0.8
Weight		g	44
Resistance & Protection			
Pollution degree	3		
Dimensions			



Certifications and compliance

Compliance

IEC/EN/BS 60669-2-2

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

IEC/EN/BS 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000041 -
 Auxiliary contact
 block