



Product designation
Product type designation
Description

Undervoltage trip
P5X14A400
Undervoltage trip
releases.
Accessories for
IEC-compliant
MCCBs

Accessories for

Operational characteristics

Rated supply voltage AC	VAC	380...440
Rated frequency	Hz	45...65
Holding consumption	VA	1.67
Release voltage	Us	35...70
Operating voltage	US	85...110
Average opening time	ms	50

Mechanical features

Tightening torque for terminals	min	Nm	0.8
	max	Nm	1
	min	lbin	7
	max	lbin	9

Conductor section	AWG/Kcmil	min	20
		max	16
	Flexible w/o lug conductor section	min	mm ² 0.5
		max	mm ² 1.5
	Flexible c/w lug conductor section	min	mm ² 0.5
		max	mm ² 1.5

Terminals	type	Screw
	tool	PZ2

Weight	g	50
--------	---	----



Wiring diagrams

Certifications and compliance

Certificates

ETIM classification

EC000066 - Power contactor, AC switching