



Product designation  
Product type designation

Description

Accessories for

Undervoltage trip  
P5X14E110UL  
Undervoltage trip  
releases for UL  
certified MCCBs.  
Accessories for  
UL-compliant  
MCCBs

#### Operational characteristics

Rated supply voltage AC	VAC	110...130
Rated supply voltage DC	VDC	110...130
Rated frequency	Hz	45...65
Holding consumption	VA	0.73
Release voltage	Us	35...70
Operating voltage	US	85...110
Average opening time	ms	50

#### Mechanical features

Tightening torque for terminals

min	Nm	0.8
max	Nm	1
min	Ibin	7
max	Ibin	9

Conductor section

AWG/Kcmil

min	20
max	16

Flexible w/o lug conductor section

min	mm <sup>2</sup>	0.5
max	mm <sup>2</sup>	1.5

Flexible c/w lug conductor section

min	mm <sup>2</sup>	0.5
max	mm <sup>2</sup>	1.5

Terminals

type	Screw
tool	PZ2

Weight

g	50
---	----



Wiring diagrams

Certifications and compliance

Certificates

cULus

ETIM classification

EC000066 - Power contactor, AC switching