



Product designation  
Product type designation  
Description

Shunt trip  
P5X16A400  
Shunt trip  
releases.  
Accessories for  
IEC-compliant  
MCCBs

Accessories for

#### Operational characteristics

Rated supply voltage AC	VAC	380...500
Rated frequency	Hz	45...65
In-rush consumption	VA	1.15
Operating voltage	US	70...110
Average opening time	ms	50

#### Mechanical features

Tightening torque for terminals			
	min	Nm	0.8
	max	Nm	1
	min	lbin	7
	max	lbin	9
Conductor section			
AWG/Kcmil	min		20
	max		16
Flexible w/o lug conductor section			
	min	mm <sup>2</sup>	0.5
	max	mm <sup>2</sup>	1.5
Flexible c/w lug conductor section			
	min	mm <sup>2</sup>	0.5
	max	mm <sup>2</sup>	1.5
Terminals			
	type		Screw
	tool		PZ2
Weight		g	50



Wiring diagrams

Certifications and compliance

Certificates

ETIM classification

EC000066 - Power contactor, AC switching