



Product designation				Monoblock actuators
Product type designation				LMPB2
General characteristics				
Colour				Red
Type of positions				Monoblock pushbutton
IEC degree of protection				IP66 on front, IP20 on terminals
Electrical characteristics				
Rated insulation voltage U_i IEC/EN	V			300
IEC Conventional free air thermal current I_{th}	A			5
UL/CSA and IEC/EN 60947-5-1 designation				B300 R300
Operating current AC12	12V	A	5	
	30V	A	5	
	125V	A	4	
	250V	A	2	
	Operating current AC15	12V	A	5
30V		A	5	
125V		A	3	
250V		A	1.5	
Operating current DC12		12V	A	1
	30V	A	1	
	125V	A	0.32	
	250V	A	0.16	
	Operating current DC13	12V	A	1
30V		A	1	
125V		A	0.22	
250V		A	0.11	
Operations				
Electrical life				cycles 250000
Mechanical features				
Mechanical life				cycles 5000000
Conductor section	AWG/kcmil conductor section	min	26	
		max	16	
IEC		min	mm ²	0.2
		max	mm ²	1.5
Ambient conditions				
Temperature				


Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

Dimensions



Wiring diagrams

