



Metallic protection guard for LP4P...B5... LP4X159

Product designation

Product type designation

**General characteristics**

Colour

Yellow

IEC degree of protection

IP65

**Ambient conditions**

Temperature

Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+80

**Dimensions**

