



Product designation	Double-touch actuators, spring return - two flush pushbuttons		
Product type designation	LPCB7113+LPXAU12		
<b>General characteristics</b>			
Colour	Green/Red		
Type of positions	Double-touch with two flush pushbuttons		
IEC degree of protection	IP66, IP67 and IP69K		
<b>Electrical characteristics</b>			
Rated insulation voltage $U_i$ IEC/EN	V	690	
IEC Conventional free air thermal current $I_{th}$	A	10	
Conductivity	1mA 5V		
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600		
Operating current AC15	12V	A	6
	24V	A	6
	48V	A	6
	120V	A	6
	240V	A	3
	400V	A	1.9
	480V	A	1.5
	500V	A	1.4
	600V	A	1.2
Operating current DC13	12V	A	3
	24V	A	3
	48V	A	1.5
	125V	A	0.55
	250V	A	0.27
	440V	A	0.15
	500V	A	0.13
600V	A	0.1	
Contact resistance	mΩ	≤20	
<b>Mechanical features</b>			
Operating force	kg-lb	<0.5Kg / 1.1lb	
Mechanical life	cycles	1000000	
Terminals screw	Screw		
Conductor section	IEC	max	mm <sup>2</sup> 1 or 2 / 2.5
Mounting adapter	LPXAU120		
<b>UL technical data</b>			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
<b>Ambient conditions</b>			
Temperature	Operating temperature	min	°C -25
		max	°C +70
		Storage temperature	
	min	°C -40	
	max	°C +85	
	<b>Certifications and compliance</b>		

Compliance

CSA C22.2 n° 14

---

IEC/EN/BS 60947-1

---

IEC/EN/BS 60947-5-1

---

UL508

---

Certificates

CCC

---

cULus

---

EAC

---

RINA

---