



Triple-touch actuators, spring return - One middle extended buttons  
LPCB7355+LPXAU120

Product designation

Product type designation

General characteristics

Colour	Green/Red/Green
Type of positions	Triple-touch
IEC degree of protection	IP66, IP67 and IP69K

Electrical characteristics

Rated insulation voltage Ui IEC/EN	V	690
IEC Conventional free air thermal current Ith	A	10
Conductivity		1mA 5V
UL/CSA and IEC/EN 60947-5-1 designation		A600 Q600

Operating current AC15

12V	A	6
24V	A	6
48V	A	6
120V	A	6
240V	A	3
400V	A	1.9
480V	A	1.5
500V	A	1.4
600V	A	1.2

Operating current DC13

12V	A	3
24V	A	3
48V	A	1.5
125V	A	0.55
250V	A	0.27
440V	A	0.15
500V	A	0.13
600V	A	0.1

Contact resistance

mΩ ≤20

Mechanical features

Operating force	kg-lb	<0.5Kg / 1.1lb
Mechanical life	cycles	1000000
Terminals screw		Screw

Conductor section

IEC

max mm<sup>2</sup> 1 or 2 / 2.5

Mounting adapter

LPXAU120

UL technical data

UL degree of protection

Type1, 2, 3R, 4, 4X, 12, 12K

Ambient conditions

Temperature

Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

Certifications and compliance

Compliance

CSA C22.2 n° 14  
IEC/EN/BS 60947-1  
IEC/EN/BS 60947-5-1  
UL508

Certificates

CCC

KIT PLASTIC TRIPLE-TOUCH ACTUATOR, SPRING RETURN, 2 EXTERNAL FLUSH AND 1 MIDDLE EXTENDED PUSHBUTTONS. SPRING RETURN, ↑ STOP ↓ WITH MOUNTING ADAPTER AND 2 CONTACT ELEMENTS, 2NO+1NC. SCREW TERMINATION

---

cULus

---

EAC

---

RINA