

Product designation	Triple-touch actuators, spring return - One middle extended buttons										
Product type designation	LPCB73										
General characteristics											
Colour	Green/Red/Green										
Type of positions	Triple-touch										
Material	Polyamide										
IEC degree of protection	IP66, IP67 and IP69K										
Mechanical features											
Operating force	kg-lb	<0.5Kg / 1.1lb									
Mechanical life	cycles	1000000									
Mounting adapter	LPXAU120										
Weight	g	30									
UL technical data											
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K										
Ambient conditions											
Temperature	<table> <tr> <td>Operating temperature</td> <td>min</td> <td>°C</td> <td>-25</td> </tr> <tr> <td></td> <td>max</td> <td>°C</td> <td>+70</td> </tr> </table>			Operating temperature	min	°C	-25		max	°C	+70
Operating temperature	min	°C	-25								
	max	°C	+70								
Storage temperature	<table> <tr> <td>min</td> <td>°C</td> <td>-40</td> </tr> <tr> <td>max</td> <td>°C</td> <td>+85</td> </tr> </table>			min	°C	-40	max	°C	+85		
min	°C	-40									
max	°C	+85									
ETIM classification											
ETIM 8.0	EC000221 - Front element for push button										