



Product designation	Double-touch actuators, spring return white indicator - Two flush pushbuttons		
Product type designation	LPCBL7123+LPXAU120		
<b>General characteristics</b>			
Colour	Green/Red		
Type of positions	Double-touch with two flush pushbuttons		
IEC degree of protection	IP66, IP67 and IP69K		
<b>Electrical characteristics</b>			
Rated insulation voltage $U_i$ IEC/EN	V	690	
IEC Conventional free air thermal current $I_{th}$	A	10	
Supply voltage (AC)	V	185...265	
Supply voltage (DC)	V	185...265	
Conductivity	1mA 5V		
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600		
Operating current AC15			
	12V	A	6
	24V	A	6
	48V	A	6
	120V	A	6
	240V	A	3
	400V	A	1.9
	480V	A	1.5
	500V	A	1.4
	600V	A	1.2
Operating current DC13			
	12V	A	3
	24V	A	3
	48V	A	1.5
	125V	A	0.55
	250V	A	0.27
	440V	A	0.15
	500V	A	0.13
	600V	A	0.1
Contact resistance		mΩ	≤20
<b>Operations</b>			
Electrical life		hours	100000
<b>Mechanical features</b>			
Operating force		kg-lb	<0.5Kg / 1.1lb
Mechanical life		cycles	1000000
Terminals screw		Screw	
Conductor section	IEC	max	mm <sup>2</sup> 1 or 2 / 2.5
Mounting adapter		LPXAU120	
<b>UL technical data</b>			
UL degree of protection		Type1, 2, 3R, 4, 4X, 12, 12K	
<b>Ambient conditions</b>			
Temperature	Operating temperature	min	°C -25
		max	°C +70
	Storage temperature	min	°C -40
		max	°C +85
<b>Certifications and compliance</b>			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		

KIT PLASTIC DOUBLE-TOUCH ACTUATOR, SPRING RETURN, WHITE INDICATOR, 2 FLUSH PUSHBUTTONS, GREEN RED/1 0 WITH MOUNTING ADAPTER AND 2 CONTACT ELEMENTS, 1NO+1NC. SCREW TERMINATION. LED INTEGRATED LAMP-HOLDER, STEADY LIGHT, 185...265VAC

---

UL508

---

Certificates

CCC

---

cULus

---

EAC

---

RINA