



Double-touch actuators, spring return white indicator - One extended and one flush pushbuttons
LPCBL7223+LPXAU120

Product designation

Product type designation

General characteristics

Colour	Green/Red		
Type of positions	Double-touch with one extended and one flush pushbuttons		
IEC degree of protection	IP66, IP67 and IP69K		
Electrical characteristics			
Rated insulation voltage Ui IEC/EN	V	690	
IEC Conventional free air thermal current Ith	A	10	
Supply voltage (AC)	V	12...30	
Supply voltage (DC)	V	12...30	
Conductivity	1mA 5V		
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600		
Operating current AC15			

12V	A	6
24V	A	6
48V	A	6
120V	A	6
240V	A	3
400V	A	1.9
480V	A	1.5
500V	A	1.4
600V	A	1.2

Operating current DC13

12V	A	3
24V	A	3
48V	A	1.5
125V	A	0.55
250V	A	0.27
440V	A	0.15
500V	A	0.13
600V	A	0.1

Contact resistance mΩ ≤20

Operations

Electrical life hours 100000

Mechanical features

Operating force kg-lb <0.5Kg / 1.1lb

Mechanical life cycles 1000000

Terminals screw Screw

Conductor section

IEC

max mm² 1 or 2 / 2.5

Mounting adapter LPXAU120

UL technical data

UL degree of protection Type1, 2, 3R, 4, 4X, 12, 12K

Ambient conditions

Temperature

Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

Certifications and compliance

Compliance

CSA C22.2 n° 14

KIT PLASTIC DOUBLE-TOUCH ACTUATOR, SPRING RETURN, WHITE INDICATOR, 1 EXTENDED AND 1 FLUSH PUSHBUTTONS, GREEN RED/ I 0 WITH MOUNTING ADAPTER AND 2 CONTACT ELEMENT, 1NO+1NC. SCREW TERMINATION. LED INTEGRATED LAMP-HOLDER, STEADY LIGHT, 12...30VAC/DC

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

CCC

cULus

EAC

RINA