



Product designation	Double-touch actuators, spring return white indicator - One extended and one flush pushbuttons LPCBL7224+LPXAU120		
Product type designation	LPCBL7224+LPXAU120		
General characteristics			
Colour	White/Black		
Type of positions	Double-touch with one extended and one flush pushbuttons		
IEC degree of protection	IP66, IP67 and IP69K		
Electrical characteristics			
Rated insulation voltage U_i IEC/EN	V	690	
IEC Conventional free air thermal current I_{th}	A	10	
Supply voltage (AC)	V	185...265	
Supply voltage (DC)	V	185...265	
Conductivity	1mA 5V		
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600		
Operating current AC15	12V	A	6
	24V	A	6
	48V	A	6
	120V	A	6
	240V	A	3
	400V	A	1.9
	480V	A	1.5
	500V	A	1.4
Operating current DC13	600V	A	1.2
	12V	A	3
	24V	A	3
	48V	A	1.5
	125V	A	0.55
	250V	A	0.27
	440V	A	0.15
Contact resistance	500V	A	0.13
	600V	A	0.1
Operations			
Electrical life	hours	100000	
Mechanical features			
Operating force	kg-lb	<0.5Kg / 1.1lb	
Mechanical life	cycles	1000000	
Terminals screw	Screw		
Conductor section	IEC	max	mm ² 1 or 2 / 2.5
Mounting adapter	LPXAU120		
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature	Operating temperature	min	°C -25
		max	°C +70
	Storage temperature	min	°C -40
		max	°C +85
Certifications and compliance			
Compliance	CSA C22.2 n° 14		

KIT PLASTIC DOUBLE-TOUCH ACTUATOR, SPRING RETURN, WHITE INDICATOR, 1 EXTENDED AND 1 FLUSH PUSHBUTTONS, WHITE BLACK/I 0 WITH MOUNTING ADAPTER AND 2 CONTACT ELEMENTS, 1NO+1NC. SCREW TERMINATION. LED INTEGRATED LAMP-HOLDER, STEADY LIGHT, 185...265VAC

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

CCC

cULus

EAC

RINA