



Product designation	Selector switch actuators lever - 2 position		
Product type designation	LPCS120+LPXAU12		
General characteristics			
Colour	Black		
Type of positions	0 - 1		
IEC degree of protection	IP66, IP67 and IP69K		
Electrical characteristics			
Rated insulation voltage U_i IEC/EN	V	690	
IEC Conventional free air thermal current I_{th}	A	10	
Conductivity	1mA 5V		
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600		
Operating current AC15			
	12V	A	6
	24V	A	6
	48V	A	6
	120V	A	6
	240V	A	3
	400V	A	1.9
	480V	A	1.5
	500V	A	1.4
	600V	A	1.2
Operating current DC13			
	12V	A	3
	24V	A	3
	48V	A	1.5
	125V	A	0.55
	250V	A	0.27
	440V	A	0.15
	500V	A	0.13
	600V	A	0.1
Contact resistance		mΩ	≤20
Mechanical features			
Mechanical life		cycles	1000000
Terminals screw	Screw		
Conductor section	IEC		
		max	mm ² 1 or 2 / 2.5
Mounting adapter	LPXAU120		
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85

Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

CCC

cULus

EAC

RINA