



Illuminated push-push button actuators - Flush LPFQL10

Product designation

Product type designation

**General characteristics**

Colour	Yellow
Type of positions	Flush pushbutton
Material	Aluminium and zinc alloy for the metal part, polyamide for plastic parts
IEC degree of protection	IP66, IP67 and IP69K

**Mechanical features**

Mechanical life - Push-Push actuators	cycles	500000
Fixing	Without mounting adapter	
Mounting adapter	LPXAU120M	


**UL technical data**

UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K
-------------------------	------------------------------

**Ambient conditions**

Temperature	Operating temperature	min	°C	-25
		max	°C	+70
	Storage temperature	min	°C	-40
		max	°C	+85

**Dimensions**



**Certifications and compliance**

Compliance	CSA C22.2 n° 14
	IEC/EN/BS 60947-1
	IEC/EN/BS 60947-5-1
	UL508

Certificates

cULus

ETIM classification

ETIM 8.0

EC000221 -  
Front element for  
push button