



Product designation	Pushbutton actuator, spring return		
Product type designation	LPSB30		
<b>General characteristics</b>			
Colour	Blue		
Type of positions	Shrouded pushbutton		
Material	Aluminium and zinc alloy for metal parts and polyamide for plastic parts		
IEC degree of protection	IP66, IP67 and IP69K		
<b>Mechanical features</b>			
Mechanical life - spring return actuators	cycles	5000000	
Fixing	Without mounting adapter		
Mounting adapter	LPXAU120M		
<b>UL technical data</b>			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
<b>Ambient conditions</b>			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
<b>Dimensions</b>			
<b>Certifications and compliance</b>			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	cULus		
<b>ETIM classification</b>			

ETIM 8.0

EC000221 -  
Front element for  
push button