



Product designation	Mushroom head pushbutton, spring return Ø 40mm/1.6" LPSB614
Product type designation	LPSB614
<b>General characteristics</b>	
Colour	Red
Type of positions	Mushroom head pushbutton
Material	Aluminium and zinc alloy for metal parts and polyamide for plastic parts
IEC degree of protection	IP66, IP67 and IP69K
<b>Mechanical features</b>	
Mechanical life - spring return actuators	cycles 5000000
Fixing	Without mounting adapter
Mounting adapter	LPXAU120M
<b>UL technical data</b>	
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K
<b>Ambient conditions</b>	
Temperature	
Operating temperature	min °C -25 max °C +70
Storage temperature	min °C -40 max °C +85
<b>Dimensions</b>	
<b>Certifications and compliance</b>	
Compliance	CSA C22.2 n° 14 IEC/EN/BS 60947-1 IEC/EN/BS 60947-5-1 UL508
Certificates	cULus

ETIM classification

ETIM 8.0

EC000221 -  
Front element for  
push button