



Product designation

Mushroom head
pushbutton,
spring return Ø
60mm/2.36"
LPSB614

Product type designation

General characteristics

Colour

Green

Type of positions

Mushroom head
pushbutton

Material

Aluminium and
zinc alloy for
metal parts and
polyamide for
plastic parts

IEC degree of protection

IP66, IP67 and
IP69K

Mechanical features

Mechanical life - spring return actuators

cycles 5000000

Fixing

Without mounting
adapter

Mounting adapter

LPXAU120M

UL technical data

UL degree of protection

Type1, 2, 3R, 4,
4X, 12, 12K

Ambient conditions

Temperature


Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

Dimensions



Spring return

Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

Certificates

cULus

ETIM classification

ETIM 8.0

EC000221 -
Front element for
push button