




| | | | |
|---|--|---------|-----|
| Product designation | Mushroom head pushbutton, spring return Ø 60mm/2.36" | | |
| Product type designation | LPSB614 | | |
| General characteristics | | | |
| Colour | Red | | |
| Type of positions | Mushroom head pushbutton | | |
| Material | Aluminium and zinc alloy for metal parts and polyamide for plastic parts | | |
| IEC degree of protection | IP66, IP67 and IP69K | | |
| Mechanical features | | | |
| Mechanical life - spring return actuators | cycles | 5000000 | |
| Fixing | Without mounting adapter | | |
| Mounting adapter | LPXAU120M | | |
| UL technical data | | | |
| UL degree of protection | Type1, 2, 3R, 4, 4X, 12, 12K | | |
| Ambient conditions | | | |
| Temperature | Operating temperature | | |
| | min | °C | -25 |
| | max | °C | +70 |
| | Storage temperature | | |
| | min | °C | -40 |
| | max | °C | +85 |

Dimensions



Spring return

Certifications and compliance

| | |
|------------|---------------------|
| Compliance | CSA C22.2 n° 14 |
| | IEC/EN/BS 60947-1 |
| | IEC/EN/BS 60947-5-1 |
| | UL508 |

Certificates

cULus

ETIM classification

ETIM 8.0

EC000221 -
Front element for
push button