



Selector switch actuators lever - 2 position LPSS12

Product designation

Product type designation

**General characteristics**

|                          |                          |
|--------------------------|--------------------------|
| Colour                   | Black                    |
| Type of positions        | 0 - 1                    |
| Material                 | Aluminium and zinc alloy |
| IEC degree of protection | IP66, IP67 and IP69K     |

**Mechanical features**

|                  |                          |         |
|------------------|--------------------------|---------|
| Mechanical life  | cycles                   | 1000000 |
| Fixing           | Without mounting adapter |         |
| Mounting adapter | LPXAU120M                |         |


**UL technical data**

|                         |                              |
|-------------------------|------------------------------|
| UL degree of protection | Type1, 2, 3R, 4, 4X, 12, 12K |
|-------------------------|------------------------------|

**Ambient conditions**

|             |                       |     |    |     |
|-------------|-----------------------|-----|----|-----|
| Temperature | Operating temperature | min | °C | -25 |
|             |                       | max | °C | +70 |
|             | Storage temperature   | min | °C | -40 |
|             |                       | max | °C | +85 |

**Dimensions**



**Certifications and compliance**

|            |                     |
|------------|---------------------|
| Compliance | CSA C22.2 n° 14     |
|            | IEC/EN/BS 60947-1   |
|            | IEC/EN/BS 60947-5-1 |
|            | UL508               |

Certificates

cULus

**ETIM classification**

|          |                           |
|----------|---------------------------|
| ETIM 8.0 | EC002611 - Control switch |
|----------|---------------------------|