



Product designation				Selector switch actuators lever - 3 position
Product type designation				LPSS130+LPXAU120
General characteristics				
Colour				Black
Type of positions				1 - 0 - 2
IEC degree of protection				IP66, IP67 and IP69K
Electrical characteristics				
Rated insulation voltage Ui IEC/EN	V			690
IEC Conventional free air thermal current Ith	A			10
Conductivity				1mA 5V
UL/CSA and IEC/EN 60947-5-1 designation				A600 Q600
Operating current AC15	12V	A	6	
	24V	A	6	
	48V	A	6	
	120V	A	6	
	240V	A	3	
	400V	A	1.9	
	480V	A	1.5	
	500V	A	1.4	
	600V	A	1.2	
	Operating current DC13	12V	A	3
24V		A	3	
48V		A	1.5	
125V		A	0.55	
250V		A	0.27	
440V		A	0.15	
500V		A	0.13	
600V		A	0.1	
Contact resistance			mΩ	≤20
Mechanical features				
Mechanical life			cycles	1000000
Terminals screw				Screw
Conductor section	IEC			
		max	mm ²	1 or 2 / 2.5
Mounting adapter				LPXAU120M
UL technical data				
UL degree of protection				Type1, 2, 3R, 4, 4X, 12, 12K
Ambient conditions				
Temperature	Operating temperature	min	°C	-25
		max	°C	+70
	Storage temperature	min	°C	-40
		max	°C	+85
Certifications and compliance				
Compliance	CSA C22.2 n° 14			
	IEC/EN/BS 60947-1			
	IEC/EN/BS 60947-5-1			

UL508

Certificates

CCC

cULus

EAC

RINA