



Product designation	Selector switch actuator key - 2 position		
Product type designation	LPSS320		
General characteristics			
Colour	Black		
Type of positions	0 - 1, key extraction in 0		
Material	Aluminium and zinc alloy		
IEC degree of protection	IP66, IP67 and IP69K		
Mechanical features			
Mechanical life	cycles	1000000	
Fixing	Without mounting adapter		
Mounting adapter	LPXAU120M		
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
Dimensions			
Certifications and compliance			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	cULus		
ETIM classification			
ETIM 8.0	EC002611 - Control switch		