



| | | | |
|--------------------------------------|---|---------|-----|
| Product designation | Selector switch actuator key - 3 position | | |
| Product type designation | LPSS35 | | |
| General characteristics | | | |
| Colour | Black | | |
| Type of positions | 1 > 0 - 2, key extraction in 0 | | |
| Material | Aluminium and zinc alloy | | |
| IEC degree of protection | IP66, IP67 and IP69K | | |
| Mechanical features | | | |
| Mechanical life | cycles | 1000000 | |
| Fixing | Without mounting adapter | | |
| Mounting adapter | LPXAU120M | | |
| UL technical data | | | |
| UL degree of protection | Type1, 2, 3R, 4, 4X, 12, 12K | | |
| Ambient conditions | | | |
| Temperature | Operating temperature | | |
| | min | °C | -25 |
| | max | °C | +70 |
| | Storage temperature | | |
| | min | °C | -40 |
| | max | °C | +85 |
| Dimensions | | | |
| | | | |
| Certifications and compliance | | | |
| Compliance | CSA C22.2 n° 14 | | |
| | IEC/EN/BS 60947-1 | | |
| | IEC/EN/BS 60947-5-1 | | |
| | UL508 | | |
| Certificates | cULus | | |
| ETIM classification | | | |
| ETIM 8.0 | EC002611 - Control switch | | |